

FISHER & PAYKEL

DATA SHEET

DishDrawer™ Dishwasher 600mm Double Integrated - Tall

Model no:

DD60DTX6I1, DD60DTX6HI1

Product Dimensions	mm
Overall height*	864 - 924
Overall width**	599
© Depth of chassis**	553
 Ventilation gap between custom panels 	8
 Height of chassis at rear (not including mounted feet) 	855
F Height of mounted feet (adjustable)	10 - 70
6 Height of toe kick custom panel (adjustable)	45 - 123
 Depth from front of drawer panel to front of toe kick panel custom panel*** prefinished panel 	40 - 100 40 - 120
① Depth of drawer opening**	527

* Includes adjustable mounted feet and the range of movement.

 ** Does not include the custom drawer panels, handles or toe kick panel to be manufactured and fitted by cabinetmaker.

*** Assuming panel thickness of 18mm.

Note: Service outlet at rear extends both sides, hoses and cords can be routed to either or both.

Minimum Clearances	mm
Minimum inside height of cavity from bottom datum	864
Minimum inside width of cavity	600
Minimum inside depth of cavity from front datum (excluding front panels)	560
Minimum ventilation gap between custom panels	8
Minimum clearance from underside of bench to top of custom panel	2
Minimum clearance from bottom of toe kick panel to floor	12
Minimum clearance from a corner cupboard	13

DATE: 08.03.2021

Ø

ß

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ±2mm (1/16"). Please read the installation manual for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com



FISHER & PAYKEL

CUSTOM PANEL PREPARATION

DishDrawer™ Dishwasher 600mm Double Integrated - Tall

```
Model no:
```

DD60DTX6I1, DD60DTX6HI1

mm
442
311
596
45 - 123
16 - 20
9
8
2
12
-
50
864
414

Maximum weight of each drawer panel (including handle) 9 kg

* The upper drawer panel may be extended up, or the lower panel down from the fixed gap between both. Adjust the height of the toe kick panel accordingly.

** If using supplied toe kick mounting screws. Panel can be fixed via screwing or gluing to the supplied mounting bracket.

*** Depending on the adjustment of leveling feet.

ISO VIEW

Ø

PROFILE VIEW

DATE: 08.03.2021

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ±2mm (1/16"). Please read the installation manual for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com

